

# PRODUCT INFORMATION PACKET



Model No: 466  
Catalog No: 466

OEM Replacement Motor, 1/4, 1/8 HP, 1 Ph, 60/50 Hz, 208-230 V, 1075 RPM, 2 Speed, 42 Frame, TEAO



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E





**Nameplate Specifications**

Output HP	1/4, 1/8 Hp	Output KW	0.19 kW
Frequency	50 Hz	Voltage	208-230 V
Current	1.4/1.2 A	Speed	1075 rpm
Service Factor	1	Phase	1
Duty	Continuous Air Over	Insulation Class	B
Frame	42	Enclosure	Totally Enclosed Air Over
Thermal Protection	Automatic	Ambient Temperature	60 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	2

**Technical Specifications**

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	6	Rotation	Clockwise Lead End
Mounting	Round Belly Band	Motor Orientation	Horizontal
Drive End Bearing	Sleeve	Opp Drive End Bearing	Sleeve
Frame Material	Rolled Steel	Shaft Type	Flat
Overall Length	16.50 in	Frame Length	3.67 in
Shaft Diameter	0.500 in	Shaft Extension	6 in
Outline Drawing	DE3G7109-S01		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022





