

PRODUCT INFORMATION PACKET



Model No: 9475

Catalog No: 9475

Fan Coil & Air Conditioner Motor, 1/6, 1/8, 1/12 HP, 1 Ph, 60/50 Hz, 230 V, 1550/1290 RPM, 3 Speed,
42 Frame, OAO



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	1/6, 1/8, 1/12 Hp	Output KW	0.13 kW
Frequency	50 Hz	Voltage	230 V
Current	1.0 A	Speed	1550/1290 rpm
Service Factor	1	Phase	1
Duty	Continuous Air Over	Insulation Class	A
Frame	42	Enclosure	Open Air Over
Thermal Protection	Automatic	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	3

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	4	Rotation	Clockwise Shaft End
Mounting	Resilient Rings	Motor Orientation	Horizontal
Drive End Bearing	Sleeve	Opp Drive End Bearing	Sleeve
Frame Material	Rolled Steel	Shaft Type	Flat
Overall Length	19.75 in	Frame Length	3.17 in
Shaft Diameter	0.500 in	Shaft Extension	7 7/8 in
Outline Drawing	DE2F7092-S01		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022

DE2F7092