

PRODUCT INFORMATION PACKET



Model No: 969A
Catalog No: 969A

OEM Replacement Motor, 1/2 HP, 1 Ph, 60 Hz, 115/230 V, 840 RPM, 1 Speed, 48 Frame, TEAO



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Phase	1	Output HP	1/2 Hp
Output KW	0.37 kW	Voltage	115/230 V
Speed	840 rpm	Service Factor	1.0
Frame	F48Y	Enclosure	Totally Enclosed Air Over
Thermal Protection	Automatic	Ambient Temperature	40 °C
Frequency	60 Hz	Current	6.1/3.1 A
Duty	Air Over	Insulation Class	B
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	8	Rotation	Counterclockwise Lead End
Mounting	Yoke	Motor Orientation	Horizontal
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Rolled Steel	Shaft Type	Double Flat
Overall Length	10.93 in	Frame Length	7.00 in
Shaft Diameter	0.625 in	Shaft Extension	2.68 in
Outline Drawing	969A-S01	Connection Drawing	614131-360

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/10/2025

