

PRODUCT INFORMATION PACKET



Model No: 97
Catalog No: 97

OEM Replacement Motor, 1/12-1/25 HP, 1 Ph, 60 Hz, 115 V, 1050 RPM, 2 Speed, 4.4" Diameter, OAO



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	1/12-1/25 Hp	Output KW	0.06 kW
Frequency	60 Hz	Voltage	115 V
Current	4.0/1.6 A	Speed	1050 rpm
Service Factor	1	Phase	1
Duty	Continuous Air Over	Insulation Class	A
Frame	4.4	Enclosure	Open Air Over
Thermal Protection	Automatic	Ambient Temperature	40 °C
UL	Recognized	CSA	N
CE	Y	Number of Speeds	2

Technical Specifications

Electrical Type	Shaded Pole	Starting Method	Across The Line
Poles	6	Rotation	Clockwise Shaft End
Mounting	Extended Studs	Motor Orientation	Horizontal
Drive End Bearing	Sleeve	Opp Drive End Bearing	Sleeve
Frame Material	Rolled Steel	Shaft Type	Flat
Overall Length	7.69 in	Shaft Diameter	0.375 in
Shaft Extension	3/8 X 3 in		
Outline Drawing	CA3J674-S01		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022

