

PRODUCT INFORMATION PACKET



Model No: 9719

Catalog No: 9719

Fan and Blower Motor, 1/4 HP, 1 Ph, 60 Hz, 208-230 V, 1075 RPM, 3 Speed, 42 Frame, OAO



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Phase	1	Output HP	1/4 Hp
Output KW	0.19 kW	Voltage	208-230 V
Speed	1075 rpm	Service Factor	1.0
Frame	42Y	Enclosure	Open Air Over
Thermal Protection	Automatic	Ambient Temperature	40 °C
Frequency	60 Hz	Current	2 A
Duty	Air Over	Insulation Class	B
UL	Recognized	CSA	Y
CE	N	Number of Speeds	3


Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	6	Rotation	Reversible
Mounting	Resilient Rings	Motor Orientation	Horizontal
Drive End Bearing	Sleeve	Opp Drive End Bearing	Sleeve
Frame Material	Rolled Steel	Shaft Type	Flat
Overall Length	11.53 in	Frame Length	4.17 in
Shaft Diameter	0.500 in	Shaft Extension	5.8 in
Outline Drawing	DE3H7034-S01		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/10/2025

CUSTOMER IS SOLELY RESPONSIBLE FOR MOTOR PERFORMANCE AND SUITABILITY IN APPLICATIONS FOR CUSTOMER'S USES.

END PLAY .005[.13] MINIMUM -.040[1.02] MAXIMUM
 MAXIMUM SHAFT RUN OUT .001[.03] PER INCH
 MAXIMUM RUN OUT NOT TO EXCEED .010[.25]



ROT: REVERSIBLE
 NAMEPLATE DATA:

Century Tipp City, OH
 THERMALLY PROTECTED

SER.DATE & PO# PLT LTR MOD DE3H034N' STK NO. 9719
 VOLTS 208-230 HZ 60 AMPS 2.0
 RPM 1075/3 SPD PH1 CAP5 MFD/370 VAC
 INS CL B AMB 40°C HP 1/4 CONT A.O. ←ROT REV→
 BRG SLV ASSEMBLED IN MEXICO

DRAWING REVISION F	REVISION BY HANNA.ZOU	DATE 07-25-2018	DRAWN BY: JRUPER	REGAL™ Regal Beloit America, Inc.	
ECO ECO-0149422	APPROVED BY DEXIAN.LI	DATE 07-25-2018			DATE: 09-23-2001
ECO DESCRIPTION SEE ECO	APPROVED BY: JRUPER				DATE: 09-23-2001
COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. (OWNER) AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.			REFERENCE	DESCRIPTION MODEL-RFHP-42FR OUTLINE	
THIRD ANGLE PROJECTION			SIZE DWG NO C DE3H7034	PROCESS/FINISH	
				SHEET 1	