

# PRODUCT INFORMATION PACKET



Model No: AR2024  
Catalog No: AR2024  
Fan and Blower Motor, 1/4 HP, 1 Ph, 60 Hz, 115 V, 1800 RPM, 48 Frame, ODP



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E





**Nameplate Specifications**

Output HP	1/4 Hp	Output KW	0.19 kW
Frequency	60 Hz	Voltage	115 V
Current	5 A	Speed	1725 rpm
Service Factor	1.35	Phase	1
Duty	Continuous	Insulation Class	B
Frame	48	Enclosure	Open Drip Proof
Thermal Protection	Automatic	Ambient Temperature	40 °C
UL	No	CSA	Y
CE	N	Number of Speeds	1

**Technical Specifications**

Electrical Type	Split Phase	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Mounting	Resilient Rings	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	10.39 in
Frame Length	4.69 in	Shaft Diameter	0.625 in
Shaft Extension	1.62 in		
Outline Drawing	AR2024-S01	Connection Drawing	621417-001A

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/28/2022