

PRODUCT INFORMATION PACKET



Model No: ARB2034L3
Catalog No: ARB2034L3
Fan and Blower Motor, 1/3-1/9 HP, 1 Ph, 60 Hz, 115 V, 1800 RPM, 56Z Frame, TEAO



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	1/3-1/9 Hp	Output KW	0.25 kW
Frequency	60 Hz	Voltage	115 V
Current	5.6/3.2 A	Speed	1725/1140 rpm
Service Factor	1	Phase	1
Duty	Continuous	Insulation Class	B
Frame	56Z	Enclosure	Totally Enclosed Air Over
Thermal Protection	No Protection	Ambient Temperature	40 °C
UL	No	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Split Phase	Starting Method	Across The Line
Poles	4/6	Rotation	Reversible
Mounting	Resilient Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	10.97 in
Frame Length	6.19 in	Shaft Diameter	0.625 in
Shaft Extension	1.62 in		
Outline Drawing	ARB2034L3-S01	Connection Drawing	620005-013A

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/28/2022