

PRODUCT INFORMATION PACKET



Model No: B116

Catalog No: B116

Pool Pump Motor, 4.0 HP, 1 Ph, 60 Hz, 208-230 V, 3600 RPM, Y56Y Frame, DP



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Phase	1	Output HP	4.0 Hp
Output KW	3.0 kW	Voltage	208-230 V
Speed	3450 rpm	Service Factor	1.25
Frame	Y56Y	Enclosure	Drip Proof
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
Frequency	60 Hz	Current	SF 21.0-19.4 A
Duty	Continuous	Insulation Class	B
UL	Recognized	CSA	Y
Number of Speeds	1		

Technical Specifications

Electrical Type	Permanent Split Capacitor, Single Or Dual Voltage	Poles	2
Rotation	Counterclockwise Pump End	Mounting	Round
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	1/2 Threaded	Overall Length	16.78 in
Frame Length	9.75 in	Shaft Diameter	0.708 in
Shaft Extension	2.75 in		
Connection Drawing	02282603-002	Outline Drawing	B116-S01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/03/2025

