

PRODUCT INFORMATION PACKET



Model No: B236
Catalog No: B236

Pool Pump Motor, 5.0 / 0.63 SPL HP, 1 Ph, 60 Hz, 230 V, 3600 RPM, R56Y Frame, DP



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	5.0 / 0.63 SPL Hp	Output KW	3.7 kW
Frequency	60 Hz	Voltage	230 V
Current	16.4/4.8 A	Speed	3450/1725 rpm
Service Factor	1	Phase	1
Duty	Continuous	Insulation Class	F
Frame	R56Y	Enclosure	Drip Proof
Thermal Protection	Thermally Protected	Ambient Temperature	50 °C
UL	Recognized	CSA	Y
Number of Speeds	2-2-VT		

Technical Specifications

Electrical Type	Permanent Split Capacitor, High Speed; Split Phase, Low Speed	Poles	2/4
Rotation	Counterclockwise Pump End	Mounting	Thru Bolt
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	3/8 Threaded	Overall Length	13.37 in
Frame Length	8.75 in	Shaft Diameter	0.500 in
Shaft Extension	2.37 in		
Connection Drawing	17888703.PCX	Outline Drawing	B236-S01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/28/2022

