

PRODUCT INFORMATION PACKET



Model No: C774
Catalog No: C774
1,1725,DP,56,1/60/208-230/115
General Purpose Motors



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	1.000 Hp	Output KW	0.75 kW
Frequency	60 Hz	Voltage	208-230/115 V
Current	6.2-6.3/12.6 A	Speed	1725 rpm
Service Factor	1.25	Phase	1
Duty	Continuous	Insulation Class	B
Frame	K56	Enclosure	Drip Proof
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications


Electrical Type	Capacitor Start, Induction Run, Single Or Dual Voltage	Starting Method	Across The Line
Poles	4	Rotation	Reversible Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	11.44 in
Frame Length	5.50 in	Shaft Diameter	0.625 in
Shaft Extension	1.94 in		
Connection Drawing	17050317.PCX	Outline Drawing	C774-S01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/11/2021

C-774

EX1900-1

A. O. SMITH CORP
ELECTRIC MOTOR DIVISION
3 HP, 230V, 60^{Hz}, 1PH, 4 POLE, CSR HERMETIC MOTOR
SPEED TORQUE CURVES
TESTED AT 230V



ST CAP = 145 MFD

RUN CAP = 40 MFD

3-7-58 W.G.J

C-774