

PRODUCT INFORMATION PACKET



Model No: DC129
Catalog No: DC129
3/4 HP SCR Motor, 2500 RPM, 90 V, 56C Frame, TEFC
SCR Motors



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	3/4 Hp	Output KW	0.56 kW
Voltage	90 V	Current	7.6 A
Speed	2500 rpm	Service Factor	1
Duty	Continuous	Insulation Class	H
Frame	SS56C	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	DC Permanent Magnet	Starting Method	Across The Line
Rotation	Reversible	Mounting	Rigid Base
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Rolled Steel	Shaft Type	Keyed
Overall Length	11.81 in	Frame Length	7.50 in
Shaft Diameter	0.625 in	Shaft Extension	2.06 in
Outline Drawing	612-0076		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/07/2021

