

PRODUCT INFORMATION PACKET



Model No: F265

Catalog No: F265

Convection Oven Motor, 1/3-.09 HP, 1 Ph, 60/50 Hz, 200-230 V, 1800 RPM, Y56Y Frame, DP



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2026 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Phase	1	Output HP	1/3-.09 Hp
Output KW	0.25 kW	Voltage	200-230 V
Speed	1725/1140 rpm	Service Factor	1.35
Frame	Y56Y	Enclosure	Drip Proof
Thermal Protection	Thermally Protected	Ambient Temperature	60 °C
Frequency	60/50 Hz	Current	2.8-2.9/1.3-1.4 A
Duty	Continuous	Insulation Class	B
UL	Recognized	CSA	Y
CE	N	Number of Speeds	2-2-VT

Technical Specifications

Electrical Type	Split Phase, Induction Run, Multi-Speed	Starting Method	Across The Line
Poles	4/6	Rotation	Reversible Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	12.25 in
Frame Length	4.75 in	Shaft Diameter	0.625 in
Shaft Extension	4 in		
Outline Drawing	18511301	Connection Drawing	18390914.PCX

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:03/04/2026

