

PRODUCT INFORMATION PACKET



Model No: H704

Catalog No: H704

Pool Pump Motor, 2.0 HP, 3 Ph, 60/50 Hz, 208-230/460 V, 3600 RPM, N56C Frame, DP



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Phase	3	Output HP	2.0 Hp
Output KW	1.5 kW	Voltage	208-230/460 V
Speed	3450/2850 rpm	Service Factor	1.2
Frame	N56C	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
Frequency	60/50 Hz	Current	5.8-5.5/2.75 A
Duty	Continuous	Insulation Class	A
UL	Recognized	CSA	Y
Number of Speeds	1		

Technical Specifications

Electrical Type	Polyphase, Induction Type, Single Or Dual Voltage	Poles	2
Rotation	Reversible Counterclockwise	Mounting	Round
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	5/8 Keyed	Overall Length	13.62 in
Frame Length	7.25 in	Shaft Diameter	0.625 in
Shaft Extension	2.07 in		
Connection Drawing	18304024.PCX	Outline Drawing	H704-S01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/18/2025

