

PRODUCT INFORMATION PACKET

FASCO®

Model No: K100
Catalog No: K100
1/100 HP C-Frame / Skeleton Motor, 2850 RPM, 120 Volts, , OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Output HP	1/100 Hp	Output KW	0.01 kW
Frequency	60 Hz	Voltage	120 V
Current	.73 A	Speed	2750 rpm
Service Factor	1	Phase	1
Duty	Air Over	Insulation Class	B
Frame	C-FRAME	Enclosure	Open Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
UL	Recognized	CSA	N
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Shaded Pole	Starting Method	Across The Line
Poles	4	Rotation	Clockwise Shaft End
Mounting	Extended Studs	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Na
Shaft Type	Groove	Overall Length	3.07 in
Shaft Diameter	0.181 in	Shaft Extension	1.05 in
Outline Drawing	71581185	Connection Drawing	NA

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022

