

PRODUCT INFORMATION PACKET

FASCO®

Model No: K610

Catalog No: K610

1/60 HP C-Frame / Skeleton Motor, 3000 RPM, 2 Speed, 120 Volts, , OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Output HP	1/60 Hp	Output KW	0.01 kW
Frequency	60 Hz	Voltage	120 V
Current	0.75-0.63 A	Speed	3000 rpm
Service Factor	1	Phase	1
Duty	Air Over	Insulation Class	B
Frame	C-FRAME	Enclosure	Open Enclosed
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
UL	Recognized	CSA	N
CE	N	Number of Speeds	2

Technical Specifications

Electrical Type	Shaded Pole	Starting Method	Across The Line
Poles	2	Rotation	Counterclockwise
Mounting	Extended Studs	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Na
Shaft Type	Flat & Groove	Overall Length	3.34 in
Shaft Diameter	0.218 in	Shaft Extension	1.33 in
Outline Drawing	7158121804_S001		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022