

PRODUCT INFORMATION PACKET

FASCO®

Model No: K670
Catalog No: K670
1/150 HP C-Frame / Skeleton Motor, 3000 RPM, 120 Volts, , OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord

**Nameplate Specifications**

Output HP	1/150 Hp	Output KW	0.01 kW
Frequency	60 Hz	Voltage	120 V
Current	.61 A	Speed	3000 rpm
Service Factor	1	Phase	1
Duty	Air Over	Insulation Class	B
Frame	C-FRAME	Enclosure	Open Enclosed
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
UL	Recognized	CSA	N
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Shaded Pole	Starting Method	Across The Line
Poles	2	Rotation	Counterclockwise Shaft End
Mounting	Extended Studs	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Na
Shaft Type	Round	Overall Length	3.69 in
Shaft Diameter	0.188 in	Shaft Extension	1.30 in
Outline Drawing	7158118805_S001	Connection Drawing	NA

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022