

PRODUCT INFORMATION PACKET



Model No: OPV747

Catalog No: OPV747

OEM Replacement Motor, 1/7, 1/11, 1/25 HP, 1 Ph, 60 Hz, 115 V, 1550/1300/1050 RPM, 3 Speed,
42 Frame, OPEN



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	1/7, 1/11, 1/25 Hp	Output KW	0.10 kW
Frequency	60 Hz	Voltage	115 V
Current	2.5/2.1/1.6 A	Speed	1550/1300/1050 rpm
Service Factor	1	Phase	1
Duty	Air Over	Insulation Class	B
Frame	42Y	Enclosure	Open Enclosed
Thermal Protection	Automatic	Ambient Temperature	50 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	3

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	4	Rotation	Counterclockwise Lead End
Mounting	Lug	Motor Orientation	Horizontal
Drive End Bearing	Sleeve	Opp Drive End Bearing	Sleeve
Frame Material	Rolled Steel	Shaft Type	Flat
Overall Length	6.75 in	Frame Length	3.67 in
Shaft Diameter	0.500 in	Shaft Extension	2-1/2 in
Outline Drawing	DE2F7110-S01		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/28/2022

3 of 5

CHUMACERA RIGIDA
HORIZONTAL

