

PRODUCT INFORMATION PACKET



Model No: ORV4538

Catalog No: ORV4538

OEM Replacement Motor, 1/4 HP, 1 Ph, 60 Hz, 115 V, 1625 RPM, 2 Speed, 42 Frame, OPEN



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Phase	1	Output HP	1/4 Hp
Output KW	0.19 kW	Voltage	115 V
Speed	1625 rpm	Service Factor	1.0
Frame	42Y	Enclosure	Open Enclosed
Thermal Protection	Automatic	Ambient Temperature	40 °C
Frequency	60 Hz	Current	3.1 A
Duty	Air Over	Insulation Class	A
UL	Recognized	CSA	Y
CE	N	Number of Speeds	2

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	4	Rotation	Clockwise Lead End
Mounting	Rigid Base	Motor Orientation	Horizontal
Drive End Bearing	Sleeve	Opp Drive End Bearing	Sleeve
Frame Material	Steel	Shaft Type	Flat
Overall Length	15.01 in	Shaft Diameter	0.500 in
Shaft Extension	5.7 X.5 X5.7 in		
Connection Drawing	7554A73F01	Outline Drawing	12201-001

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/10/2025

