

PRODUCT INFORMATION PACKET



Model No: P123

Catalog No: P123

Close-Coupled Pump Motor, 1.5 HP, 1 Ph, 60 Hz, 230/115 V, 1800 RPM, R145JM Frame, DP



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	1.5 Hp	Output KW	1.1 kW
Frequency	60 Hz	Voltage	230/115 V
Current	7.5/15.0 A	Speed	1725 rpm
Service Factor	1.15	Phase	1
Duty	Continuous	Insulation Class	B
Frame	R145JM	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N		

Technical Specifications

Electrical Type	Capacitor Start, Capacitor Run, Single Or Dual Voltage	Starting Method	Across The Line
Poles	4	Rotation	Reversible Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	JM	Overall Length	16.29 in
Frame Length	8.75 in	Shaft Diameter	1.156 in
Shaft Extension	4.28 in		
Outline Drawing	P123-S01	Connection Drawing	17050308.PCX

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/30/2023

