

PRODUCT INFORMATION PACKET



Model No: RA1076

Catalog No: RA1076

Fan Coil & Air Conditioner Motor, 3/4 HP, 1 Ph, 60 Hz, 208-230 V, 1075 RPM, 3 Speed, 48 Frame,
SEMI ENCL



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2024 Regal Rexnord Corporation, All Rights Reserved. MC017097E






Nameplate Specifications

Phase	1	Output HP	3/4 Hp
Output KW	0.56 kW	Voltage	208-230 V
Speed	1075 rpm	Service Factor	1.0
Frame	48Y	Enclosure	Semi Enclosed
Thermal Protection	Automatic	Efficiency	66.1 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	3.6 A	Duty	Air Over
Insulation Class	A	UL	Recognized
CSA	Y	CE	N
Number of Speeds	3		

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	6	Rotation	Counterclockwise Lead End
Mounting	Resilient Ring/Extended Studs	Motor Orientation	Horizontal
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Rolled Steel	Shaft Type	Flat
Overall Length	20.00 in	Frame Length	4.75 in
Shaft Diameter	0.500 in	Shaft Extension	7.4 X.5 X7.3 in
Outline Drawing	RA1076-S01	Connection Drawing	614131-106

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/17/2024



NOTES:

1. FOR USE WITH 614129 OR 2513020-001 NAMEPLATE BLANKS
2. _____ INDICATES DIMENSION LIMITS

DRAWING REVISION		REVISION BY	DATE	TOLERANCES UNLESS OTHERWISE SPECIFIED		DRAWN BY:		 Regal Beloit America, Inc.	
ECO		J. RUPERT	09-08-2022	DEC. INCH mm ANGLE		PZ			
NMR-0216370		J. RUPERT	09-08-2022	X ±0.1 [±2.5] ±0.5°		DATE:		04-12-2011	
ECO DESCRIPTION		REVISED FOR UP ISSUE		.XX ±0.02 [±0.51]		APPROVED BY:		Tiger Wong	
COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. (OWNER) AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.				.XXX ±0.005 [±0.127]		DATE:		04-12-2011	
				.XXXX ±0.0005 [±0.0127]		REMOVE BURRS & BREAK SHARP		REFERENCE	
				EDGES .003/.015 [0.076/.381] X 45°		CORNER FILLETS R.02 [51]		THIRD ANGLE PROJECTION	
				MACHINED SURFACES .125 [3.175] mm		mm SHOWN IN [BRACKETS]		SIZE DWG NO	
								C	
								SHEET	
								1	