

PRODUCT INFORMATION PACKET

FASCO®

Model No: UB588
Catalog No: UB588
4 WATT Refrigeration Motor, 1450 RPM, 115 Volts, Unit Bearing, TEAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord

**Nameplate Specifications**

Phase	1	Output Watts	4 W
Voltage	115 V	Speed	1450 rpm
Service Factor	1	Frame	UNIT BEARING
Enclosure	Totally Enclosed Air Over	Thermal Protection	Impedance
Ambient Temperature	40 °C	Frequency	60 Hz
Current	0.29 A	Duty	Continuous
Insulation Class	B	UL	Recognized
CSA	Y	CE	N
Number of Speeds	1		

Technical Specifications

Electrical Type	Shaded Pole	Starting Method	Across The Line
Poles	4	Rotation	Clockwise Opposite Shaft End
Mounting	2 BOSS/OSE 3 HOLES	Drive End Bearing	Unit
Opp Drive End Bearing	Unit	Frame Material	Cast Iron
Shaft Type	Threaded	Frame Length	2.87 in
Shaft Diameter	1/4x20 in	Shaft Extension	.415 in
Outline Drawing	UB588-S01		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:08/24/2023

