

PRODUCT INFORMATION PACKET



Model No: YA2030
Catalog No: YA2030

OEM Replacement Motor, 1/3 HP, 1 Ph, 60 Hz, 115 V, 1800 RPM, 48YZ Frame, ENCLOSED



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Phase	1	Output HP	1/3 Hp
Output KW	0.25 kW	Voltage	115 V
Speed	1725 rpm	Service Factor	1.0
Frame	48YZ	Enclosure	Totally Enclosed
Thermal Protection	Automatic	Ambient Temperature	40 °C
Frequency	60 Hz	Current	6.0 A
Duty	Continuous	Insulation Class	B
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Split Phase	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Mounting	Yoke	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Rolled Steel
Shaft Type	Flat	Overall Length	10.28 in
Frame Length	5.44 in	Shaft Diameter	0.500 in
Shaft Extension	1.88 in		
Connection Drawing	621417-011A	Outline Drawing	YA2030-S01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/27/2023

