

# PRODUCT INFORMATION PACKET

FASCO®

Model No: D0418

Catalog No: D0418

Ventilation Motor, 1/15 HP, 1 Ph, 60 Hz, 115/230 V, 3000 RPM, 1 Speed, 3.3" Diameter, TEFC



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



**Nameplate Specifications**

Phase	1	Output HP	1/15 Hp
Output KW	0.05 kW	Voltage	115/230 V
Speed	3000 rpm	Service Factor	1
Frame	3.3	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
Frequency	60 Hz	Current	2.00/1.00 A
Duty	Air Over	Insulation Class	B
UL	Recognized	CSA	N
CE	N	Number of Speeds	1

**Technical Specifications**

Electrical Type	Shaded Pole	Starting Method	Across The Line
Poles	2	Rotation	Counterclockwise Shaft End
Mounting	Extended Studs	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Steel
Shaft Type	Flat	Overall Length	9.55 in
Frame Length	3.40 in	Shaft Diameter	0.312 in
Shaft Extension	5 in		
Outline Drawing	712112940-S01	Connection Drawing	SEE OUTLINE

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:03/01/2025