

# PRODUCT INFORMATION PACKET

FASCO®

Model No: D0746

Catalog No: D0746

OEM Replacement Motor, 1/12 HP, 1 Ph, 60 Hz, 115 V, 1550/1300 RPM, 2 Speed, 3.3" Diameter, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



**Nameplate Specifications**

Output HP	1/12 Hp	Output KW	0.06 kW
Frequency	60 Hz	Voltage	115 V
Current	1.10/0.73 A	Speed	1550/1300 rpm
Service Factor	1	Phase	1
Duty	Air Over	Insulation Class	B
Frame	3.3	Enclosure	Open Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	50 °C
UL	Recognized	CSA	N
CE	N	Number of Speeds	2

**Technical Specifications**

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	4	Rotation	Clockwise Shaft End
Mounting	Lug	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Steel
Shaft Type	Flat	Overall Length	7.38 in
Frame Length	3.93 in	Shaft Diameter	0.375 in
Shaft Extension	3.45 in		
Outline Drawing	71903481-S01	Connection Drawing	00469082

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022