

PRODUCT INFORMATION PACKET

FASCO®

Model No: D091

Catalog No: D091

Ventilation Motor, 1/15 HP, 1 Ph, 60 Hz, 115/230 V, 3000 RPM, 1 Speed, 3.3" Diameter, TEFC



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Output HP	1/15 Hp	Output KW	0.05 kW
Frequency	60 Hz	Voltage	115/230 V
Current	2.00/1.00 A	Speed	3000 rpm
Service Factor	1	Phase	1
Duty	Air Over	Insulation Class	B
Frame	3.3	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
UL	Recognized	CSA	N
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Shaded Pole	Starting Method	Across The Line
Poles	2	Rotation	Clockwise Shaft End
Mounting	Extended Studs	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Steel
Shaft Type	Flat	Overall Length	9.55 in
Frame Length	4.50 in	Shaft Diameter	0.312 in
Shaft Extension	5.0 in		
Connection Drawing	SEE OUTLINE	Outline Drawing	712112939-S01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022