

PRODUCT INFORMATION PACKET

FASCO®

Model No: D1005

Catalog No: D1005

OEM Replacement Motor, 1/10 HP, 1 Ph, 60 Hz, 460 V, 1075 RPM, 2 Speed, 42 Frame, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Output HP	1/10 Hp	Output KW	0.07 kW
Frequency	60 Hz	Voltage	460 V
Current	0.50 A	Speed	1075 rpm
Service Factor	1	Phase	1
Duty	Continuous	Insulation Class	B
Frame	42	Enclosure	Open Air Over
Thermal Protection	Automatic	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	2

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	6	Rotation	Clockwise Shaft End
Mounting	Resilient Base	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Na
Shaft Type	Flat	Overall Length	22.52 in
Shaft Diameter	0.500 in	Shaft Extension	9.625 in
Connection Drawing	SEE OUTLINE	Outline Drawing	7186032202_S001

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022