

# PRODUCT INFORMATION PACKET

FASCO®

Model No: D1008

Catalog No: D1008

OEM Replacement Motor, 1/10 HP, 1 Ph, 60 Hz, 115 V, 1550 RPM, 1 Speed, 4.4" Diameter, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



**Nameplate Specifications**

|                    |                     |                     |               |
|--------------------|---------------------|---------------------|---------------|
| Output HP          | 1/10 Hp             | Output KW           | 0.07 kW       |
| Frequency          | 60 Hz               | Voltage             | 115 V         |
| Current            | 4.4 A               | Speed               | 1550 rpm      |
| Service Factor     | 1                   | Phase               | 1             |
| Duty               | Air Over            | Insulation Class    | B             |
| Frame              | 4.4                 | Enclosure           | Open Air Over |
| Thermal Protection | Thermally Protected | Ambient Temperature | 40 °C         |
| UL                 | Recognized          | CSA                 | Y             |
| CE                 | N                   | Number of Speeds    | 1             |

**Technical Specifications**

|                       |                 |                    |                     |
|-----------------------|-----------------|--------------------|---------------------|
| Electrical Type       | Shaded Pole     | Starting Method    | Across The Line     |
| Poles                 | 4               | Rotation           | Clockwise Shaft End |
| Mounting              | Lug             | Drive End Bearing  | Sleeve              |
| Opp Drive End Bearing | Sleeve          | Frame Material     | Na                  |
| Shaft Type            | Flat            | Overall Length     | 5.35 in             |
| Shaft Diameter        | 0.500 in        | Shaft Extension    | 1.8 in              |
| Outline Drawing       | 7108712702_S001 | Connection Drawing | NA                  |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022