

PRODUCT INFORMATION PACKET

FASCO®

Model No: D1069

Catalog No: D1069

1/10-1/15 HP OEM Replacement Motor, 1040 RPM, 2 Speed, 115 Volts, 42 Frame, OAO
OEM Replacement Motors



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

| | | | |
|--------------------|---------------------|---------------------|---------------|
| Output HP | 1/10-1/15 Hp | Output KW | 0.07 kW |
| Frequency | 60 Hz | Voltage | 115 V |
| Current | 3.5 A | Speed | 1050 rpm |
| Service Factor | 1 | Phase | 1 |
| Duty | Air Over | Insulation Class | A |
| Frame | 42 | Enclosure | Open Air Over |
| Thermal Protection | Thermally Protected | Ambient Temperature | 40 °C |
| UL | Recognized | CSA | Y |
| CE | N | Number of Speeds | 2 |

Technical Specifications

| | | | |
|-----------------------|-----------------|--------------------|----------------------------|
| Electrical Type | Shaded Pole | Starting Method | Across The Line |
| Poles | 6 | Rotation | Counterclockwise Shaft End |
| Mounting | Extended Studs | Drive End Bearing | Sleeve |
| Opp Drive End Bearing | Sleeve | Frame Material | Na |
| Shaft Type | Flat | Overall Length | 8.63 in |
| Shaft Diameter | 0.375 in | Shaft Extension | 3.00 in |
| Outline Drawing | 7151340709_S001 | Connection Drawing | SEE OUTLINE |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/11/2021