

PRODUCT INFORMATION PACKET

FASCO®

Model No: D1082
Catalog No: D1082
1/8 HP OEM Replacement Motor, 1070 RPM, 115 Volts, 42 Frame, OAO
OEM Replacement Motors



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Output HP	1/8 Hp	Output KW	0.10 kW
Frequency	60 Hz	Voltage	115 V
Current	6.0 A	Speed	1070 rpm
Service Factor	1	Phase	1
Duty	Air Over	Insulation Class	A
Frame	42	Enclosure	Open Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Shaded Pole	Starting Method	Across The Line
Poles	6	Rotation	Clockwise Shaft End
Mounting	Lug	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Flat	Overall Length	7.34 in
Frame Length	3.63 in	Shaft Diameter	0.500 in
Shaft Extension	3.25 in		
Connection Drawing	NA	Outline Drawing	7152006714_S001

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/11/2021