

# PRODUCT INFORMATION PACKET

FASCO®

Model No: D1089

Catalog No: D1089

OEM Replacement Motor, 1/15 HP, 1 Ph, 60 Hz, 115 V, 850-620-520 RPM, 3 Speed, 42 Frame, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



**Nameplate Specifications**

Output HP	1/15 Hp	Output KW	0.05 kW
Frequency	60 Hz	Voltage	115 V
Current	1.3 A	Speed	850-620-520 rpm
Service Factor	1	Phase	1
Duty	Continuous	Insulation Class	B
Frame	42	Enclosure	Open Air Over
Thermal Protection	Automatic	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	3

**Technical Specifications**

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	8	Rotation	Reversible
Mounting	Resilient Rings	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Na
Shaft Type	Flat	Overall Length	7.09 in
Shaft Diameter	0.500 in	Shaft Extension	3 in
Connection Drawing	SEE OUTLINE	Outline Drawing	7186007008_S001

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022