


PRODUCT INFORMATION PACKET

FASCO®

Model No: D1102

Catalog No: D1102

OEM Replacement Motor, 1/20 HP, 1 Ph, 60 Hz, 115/230 V, 1550 RPM, 1 Speed, 3.3" Diameter, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Output HP	1/20 Hp	Output KW	0.04 kW
Frequency	60 Hz	Voltage	115/230 V
Current	0.75/0.40 A	Speed	1550 rpm
Service Factor	1	Phase	1
Duty	Air Over	Insulation Class	B
Frame	3.3	Enclosure	Open Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	4	Rotation	Clockwise Shaft End
Mounting	Extended Studs	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Steel
Shaft Type	Flat	Overall Length	6.41 in
Frame Length	3.24 in	Shaft Diameter	0.313 in
Shaft Extension	2.70 in		
Outline Drawing	71902885	Connection Drawing	00464132

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022