

PRODUCT INFORMATION PACKET

FASCO®

Model No: D1125

Catalog No: D1125

OEM Replacement Motor, 1/20 / 1/15 HP, 1 Ph, 50/60 Hz, 208-230 V, 1400/1550 RPM, 1 Speed,
3.3" Diameter, OAO



Regal and FASCO are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Phase	1	Output HP	1/20 / 1/15 Hp
Output KW	0.04 kW	Voltage	208-230 V
Speed	1400/1550 rpm	Service Factor	1
Frame	3.3	Enclosure	Open Air Over
Thermal Protection	Thermally Protected	Efficiency	54 %
Ambient Temperature	40 °C	Frequency	50/60 Hz
Current	0.40/0.50 A	Duty	Air Over
Insulation Class	B	UL	Recognized
CSA	N	CE	N
Number of Speeds	1		

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	4	Rotation	Counterclockwise Shaft End
Mounting	Extended Studs	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Steel
Shaft Type	Flat	Overall Length	6.75 in
Frame Length	3.62 in	Shaft Diameter	0.313 in
Shaft Extension	2.64 in		
Connection Drawing	00469085	Outline Drawing	71902084

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/23/2025