

# PRODUCT INFORMATION PACKET

FASCO®

Model No: D1129

Catalog No: D1129

Refrigeration Motor, 1/20 HP, 1 Ph, 50 Hz, 115/230 V, 1550/1350 RPM, 1 Speed, 3.3" Diameter, TEAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



**Nameplate Specifications**

Output HP	1/20 Hp	Output KW	0.04 kW
Frequency	50 Hz	Voltage	115/230 V
Current	0.70/0.35 A	Speed	1550/1350 rpm
Service Factor	1	Phase	1
Duty	Air Over	Insulation Class	B
Frame	3.3	Enclosure	Totally Enclosed Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

**Technical Specifications**

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	4	Rotation	Clockwise Shaft End
Mounting	Lug	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Steel
Shaft Type	Flat	Overall Length	4.86 in
Frame Length	2.95 in	Shaft Diameter	0.312 in
Shaft Extension	1.63 in		
Outline Drawing	71903144	Connection Drawing	00469209

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022