

PRODUCT INFORMATION PACKET

FASCO®

Model No: D1144

Catalog No: D1144

OEM Replacement Motor, 1/25 HP, 1 Ph, 60 Hz, 115 V, 1200 RPM, 3 Speed, 3.3" Diameter, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Phase	1	Output HP	1/25 Hp
Output KW	0.03 kW	Voltage	115 V
Speed	1200 rpm	Service Factor	1
Frame	3.3	Enclosure	Open Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
Frequency	60 Hz	Current	1.10 A
Duty	Air Over	Insulation Class	B
UL	Recognized	CSA	Y
CE	N	Number of Speeds	3

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	6	Rotation	Clockwise Shaft End
Mounting	Resilient Rings	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Steel
Shaft Type	Flat	Overall Length	10.43 in
Frame Length	4.51 in	Shaft Diameter	0.375 in
Shaft Extension	5.68 in		
Outline Drawing	71902355	Connection Drawing	00469105

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/10/2025