

# PRODUCT INFORMATION PACKET

FASCO®

Model No: D1169  
Catalog No: D1169

OEM Replacement Motor, 1/10 HP, 1 Ph, 50 Hz, 208-230 V, 3000 RPM, 1 Speed, 3.3" Diameter, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



**Nameplate Specifications**

Output HP	1/10 Hp	Output KW	0.07 kW
Frequency	50 Hz	Voltage	208-230 V
Current	1.5/1.4 A	Speed	3000 rpm
Phase	1	Duty	Air Over
Insulation Class	B	Frame	3.3
Enclosure	Open Air Over	Thermal Protection	Thermally Protected
Ambient Temperature	40 °C	UL	Recognized
CSA	Y	CE	N
Number of Speeds	1		

**Technical Specifications**

Electrical Type	Shaded Pole	Starting Method	Across The Line
Poles	2	Rotation	Counterclockwise Shaft End
Mounting	Lug	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Steel
Shaft Type	Flat	Overall Length	6.99 in
Frame Length	3.43 in	Shaft Diameter	0.313 in
Shaft Extension	1.1 in		
Connection Drawing	SEE OUTLINE	Outline Drawing	71217730

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022