

# PRODUCT INFORMATION PACKET

FASCO®

Model No: D1182

Catalog No: D1182

OEM Replacement Motor, 1/16 HP, 1 Ph, 60 Hz, 208-230 V, 3450 RPM, 1 Speed, 3.3" Diameter, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



**Nameplate Specifications**

Output HP	1/16 Hp	Output KW	0.04 kW
Frequency	60 Hz	Voltage	208-230 V
Current	.6 A	Speed	3450 rpm
Service Factor	1	Phase	1
Duty	Air Over	Insulation Class	B
Frame	3.3	Enclosure	Open Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

**Technical Specifications**

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	2	Rotation	Counterclockwise Shaft End
Mounting	Extended Studs	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Steel
Shaft Type	Double Flat	Overall Length	8.16 in
Frame Length	4.33 in	Shaft Diameter	0.312 in
Shaft Extension	3.35 in		
Outline Drawing	71624163	Connection Drawing	00469127

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022