

PRODUCT INFORMATION PACKET

FASCO®

Model No: D1190

Catalog No: D1190

OEM Replacement Motor, 1/30 HP, 1 Ph, 60 Hz, 115 V, 3300 RPM, 1 Speed, 3.3" Diameter, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Output HP	1/30 Hp	Output KW	0.02 kW
Frequency	60 Hz	Voltage	115 V
Current	1.55 A	Speed	3300 rpm
Phase	1	Duty	Air Over
Insulation Class	B	Frame	3.3
Enclosure	Open Air Over	Thermal Protection	Thermally Protected
Ambient Temperature	40 °C	UL	Recognized
CSA	Y	CE	N
Number of Speeds	1		

Technical Specifications

Electrical Type	Shaded Pole	Starting Method	Across The Line
Poles	2	Rotation	Clockwise Shaft End
Mounting	Lug	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Steel
Shaft Type	Flat	Overall Length	7.08 in
Frame Length	4.62 in	Shaft Diameter	0.313 in
Shaft Extension	1.75 in		
Connection Drawing	NA	Outline Drawing	71218253

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022