

PRODUCT INFORMATION PACKET

FASCO®

Model No: D152

Catalog No: D152

Fan and Blower Motor, 1/4-1/5-1/6-1/8 HP, 1 Ph, 60 Hz, 277 V, 1050 RPM, 4 Speed, 42 Frame, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Phase	1	Output HP	1/4-1/5-1/6-1/8 Hp
Output KW	0.19 kW	Voltage	277 V
Speed	1050 rpm	Service Factor	1
Frame	42	Enclosure	Open Air Over
Thermal Protection	Automatic	Ambient Temperature	40 °C
Frequency	60 Hz	Current	1.6/1.1/0.9/0.7 A
Duty	Continuous	Insulation Class	B
UL	Recognized	CSA	Y
CE	N	Number of Speeds	4

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	6	Rotation	Reversible
Mounting	Extended Studs	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Na
Shaft Type	Flat	Overall Length	10.97 in
Shaft Diameter	0.500 in	Shaft Extension	6.00 in
Connection Drawing	SEE OUTLINE	Outline Drawing	7186001008_S001

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/10/2025