

# PRODUCT INFORMATION PACKET

FASCO®

Model No: D167

Catalog No: D167

Fan and Blower Motor, 1/70 HP, 1 Ph, 60 Hz, 115 V, 1500 RPM, 1 Speed, 3.3" Diameter, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



**Nameplate Specifications**

Output HP	<b>1/70 Hp</b>	Output KW	<b>0.01 kW</b>
Frequency	<b>60 Hz</b>	Voltage	<b>115 V</b>
Current	<b>0.70 A</b>	Speed	<b>1500 rpm</b>
Phase	<b>1</b>	Duty	<b>Air Over</b>
Insulation Class	<b>B</b>	Frame	<b>3.3</b>
Enclosure	<b>Open Air Over</b>	Thermal Protection	<b>Thermally Protected</b>
Ambient Temperature	<b>40 °C</b>	UL	<b>Recognized</b>
CSA	<b>Y</b>	CE	<b>N</b>
Number of Speeds	<b>1</b>		

**Technical Specifications**

Electrical Type	<b>Shaded Pole</b>	Starting Method	<b>Across The Line</b>
Poles	<b>4</b>	Rotation	<b>Clockwise Shaft End</b>
Mounting	<b>Extended Studs</b>	Drive End Bearing	<b>Sleeve</b>
Opp Drive End Bearing	<b>Sleeve</b>	Frame Material	<b>Steel</b>
Shaft Type	<b>Flat</b>	Overall Length	<b>6.38 in</b>
Frame Length	<b>2.82 in</b>	Shaft Diameter	<b>0.250 in</b>
Shaft Extension	<b>3.00 in</b>		
Outline Drawing	<b>71631489</b>	Connection Drawing	<b>NA</b>

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022