

# PRODUCT INFORMATION PACKET

FASCO®

Model No: D174

Catalog No: D174

Fan and Blower Motor, 1/10 HP, 1 Ph, 60 Hz, 115 V, 1500 RPM, 1 Speed, 4.4" Diameter, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



**Nameplate Specifications**

Output HP	1/10 Hp	Output KW	0.07 kW
Frequency	60 Hz	Voltage	115 V
Current	3.5 A	Speed	1500 rpm
Service Factor	1	Phase	1
Duty	Air Over	Insulation Class	A
Frame	4.4	Enclosure	Open Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

**Technical Specifications**

Electrical Type	Shaded Pole	Starting Method	Across The Line
Poles	4	Rotation	Clockwise Shaft End
Mounting	Extended Studs	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Na
Shaft Type	Flat	Overall Length	6.99 in
Shaft Diameter	0.375 in	Shaft Extension	2.9 in
Connection Drawing	NA	Outline Drawing	7108016734_S001

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022