

# PRODUCT INFORMATION PACKET

**FASCO**®

Model No: D208

Catalog No: D208

Fan and Blower Motor, 1/30 HP, 1 Ph, 60 Hz, 115 V, 3000 RPM, 1 Speed, 3.3" Diameter, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

**RegalRexnord**



### Nameplate Specifications

|                    |                     |                     |               |
|--------------------|---------------------|---------------------|---------------|
| Output HP          | 1/30 Hp             | Output KW           | 0.02 kW       |
| Frequency          | 60 Hz               | Voltage             | 115 V         |
| Current            | 1.1 A               | Speed               | 3000 rpm      |
| Service Factor     | 1                   | Phase               | 1             |
| Duty               | Air Over            | Insulation Class    | B             |
| Frame              | 3.3                 | Enclosure           | Open Air Over |
| Thermal Protection | Thermally Protected | Ambient Temperature | 40 °C         |
| UL                 | Recognized          | CSA                 | Y             |
| CE                 | N                   | Number of Speeds    | 1             |

### Technical Specifications

|                       |                |                    |                     |
|-----------------------|----------------|--------------------|---------------------|
| Electrical Type       | Shaded Pole    | Starting Method    | Across The Line     |
| Poles                 | 2              | Rotation           | Clockwise Shaft End |
| Mounting              | Extended Studs | Drive End Bearing  | Sleeve              |
| Opp Drive End Bearing | Sleeve         | Frame Material     | Steel               |
| Shaft Type            | Flat           | Overall Length     | 6.95 in             |
| Frame Length          | 3.40 in        | Shaft Diameter     | 0.250 in            |
| Shaft Extension       | 3.00 in        |                    |                     |
| Outline Drawing       | 71211695       | Connection Drawing | NA                  |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022