

PRODUCT INFORMATION PACKET

FASCO®

Model No: D228

Catalog No: D228

Fan and Blower Motor, 1/50 HP, 1 Ph, 60 Hz, 115 V, 3000 RPM, 1 Speed, 3.3" Diameter, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

| | | | |
|---------------------|---------------|--------------------|---------------------|
| Output HP | 1/50 Hp | Output KW | 0.01 kW |
| Frequency | 60 Hz | Voltage | 115 V |
| Current | 0.92 A | Speed | 3000 rpm |
| Phase | 1 | Duty | Air Over |
| Insulation Class | B | Frame | 3.3 |
| Enclosure | Open Air Over | Thermal Protection | Thermally Protected |
| Ambient Temperature | 40 °C | UL | Recognized |
| CSA | Y | CE | N |
| Number of Speeds | 1 | | |

Technical Specifications

| | | | |
|-----------------------|----------------|-------------------|---------------------|
| Electrical Type | Shaded Pole | Starting Method | Across The Line |
| Poles | 2 | Rotation | Clockwise Shaft End |
| Mounting | Extended Studs | Drive End Bearing | Sleeve |
| Opp Drive End Bearing | Sleeve | Frame Material | Steel |
| Shaft Type | Flat | Overall Length | 5.03 in |
| Frame Length | 2.24 in | Shaft Diameter | 0.250 in |
| Shaft Extension | 2.00 in | | |
| Connection Drawing | NA | Outline Drawing | 71219952 |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022