

PRODUCT INFORMATION PACKET

FASCO®

Model No: D245

Catalog No: D245

Fan Coil & Air Conditioner Motor, 1/3-1/5 HP, 1 Ph, 60 Hz, 230 V, 1050 RPM, 2 Speed, 42 Frame, OAO



Regal and FASCO are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2026 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Phase	1	Output HP	1/3-1/5 Hp
Output KW	0.25 kW	Voltage	230 V
Speed	1050 rpm	Service Factor	1
Frame	42	Enclosure	Open Air Over
Thermal Protection	Automatic	Ambient Temperature	40 °C
Frequency	60 Hz	Current	2.7-1.6 A
Duty	Continuous	Insulation Class	B
UL	Recognized	CSA	Y
CE	N	Number of Speeds	2

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	6	Rotation	Clockwise Lead End
Mounting	Resilient Rings	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Na
Shaft Type	Flat	Overall Length	20.60 in
Shaft Diameter	0.500 in	Shaft Extension	8.00 in
Outline Drawing	7186002406_S001	Connection Drawing	SEE OUTLINE

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/07/2026