

PRODUCT INFORMATION PACKET

FASCO®

Model No: D247

Catalog No: D247

Fan Coil & Air Conditioner Motor, 1/6-1/8-1/12 HP, 1 Ph, 60 Hz, 230 V, 1550 RPM, 3 Speed, 42 Frame,
OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Phase	1	Output HP	1/6-1/8-1/12 Hp
Output KW	0.13 kW	Voltage	230 V
Speed	1550 rpm	Service Factor	1
Frame	42	Enclosure	Open Air Over
Thermal Protection	Automatic	Efficiency	44 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	1.0/0.7/0.5 A	Duty	Continuous
Insulation Class	B	UL	Recognized
CSA	Y	CE	N
Number of Speeds	3		

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	4	Rotation	Counterclockwise Lead End
Mounting	Resilient Rings	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Na
Shaft Type	Flat	Overall Length	19.82 in
Shaft Diameter	0.500 in	Shaft Extension	8.00 in
Connection Drawing	SEE OUTLINE	Outline Drawing	7184000711_S001

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/11/2023