

# PRODUCT INFORMATION PACKET

FASCO®

Model No: D251

Catalog No: D251

1/15-1/35-1/50 HP Fan Coil / Room Air Conditioner Motor, 1050 RPM, 3 Speed, 208/230 Volts, 42 Frame, OAO  
Fan Coil & Air Conditioner Motors



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



**Nameplate Specifications**

Output HP	1/15-1/35-1/50 Hp	Output KW	0.05 kW
Frequency	60 Hz	Voltage	208/230 V
Current	1.2/0.5/0.4 A	Speed	1050 rpm
Service Factor	1	Phase	1
Duty	Air Over	Insulation Class	A
Frame	42	Enclosure	Open Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	3

**Technical Specifications**

Electrical Type	Shaded Pole	Starting Method	Across The Line
Poles	6	Rotation	Counterclockwise Shaft End
Mounting	Resilient Base	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Na
Shaft Type	Flat	Overall Length	20.85 in
Shaft Diameter	0.500 in	Shaft Extension	9.25 in
Connection Drawing	SEE OUTLINE	Outline Drawing	7151301526_S001

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/11/2021