

PRODUCT INFORMATION PACKET

FASCO®

Model No: D262

Catalog No: D262

OEM Replacement Motor, 1/5 HP, 1 Ph, 60 Hz, 230 V, 925 RPM, 1 Speed, 42 Frame, OAO



Regal and FASCO are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Phase	1	Output HP	1/5 Hp
Output KW	0.15 kW	Voltage	230 V
Speed	925 rpm	Service Factor	1
Frame	42	Enclosure	Open Air Over
Thermal Protection	Automatic	Ambient Temperature	40 °C
Frequency	60 Hz	Current	2.3 A
Duty	Continuous	Insulation Class	B
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	6	Rotation	Reversible
Mounting	Extended Studs	Drive End Bearing	Sleeve
Opp Drive End Bearing	Sleeve	Frame Material	Na
Shaft Type	Flat	Overall Length	8.06 in
Shaft Diameter	0.500 in	Shaft Extension	4 in
Connection Drawing	SEE OUTLINE	Outline Drawing	71860006

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:05/12/2025