

PRODUCT INFORMATION PACKET

FASCO®

Model No: D2850

Catalog No: D2850

OEM Replacement Motor, 1-3/4 HP, 1 Ph, 60 Hz, 208-230/460 V, 1125/950 RPM, 1 Speed, 48 Frame, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Output HP	1-3/4 Hp	Output KW	0.75 kW
Frequency	60 Hz	Voltage	208-230/460 V
Current	3.95/2.10 A	Speed	1125/950 rpm
Service Factor	1	Phase	1
Duty	Continuous Air Over	Insulation Class	B
Frame	48	Enclosure	Open Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	65 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Permanent Split Capacitor	Poles	6
Rotation	Counterclockwise	Mounting	Lug
Motor Orientation	Any	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Double Flat	Overall Length	9.88 in
Frame Length	5.82 in	Shaft Diameter	0.500 in
Shaft Extension	2.92 in	Thru-bolts Extension	0.14 in
Outline Drawing	5KCP39UFWD74S	Connection Drawing	NP24X327426

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022