

PRODUCT INFORMATION PACKET

FASCO®

Model No: D2851

Catalog No: D2851

OEM Replacement Motor, 1-3/4 HP, 1 Ph, 60 Hz, 208-230/460 V, 1125/950 RPM, 1 Speed, 48 Frame, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

Output HP	1-3/4 Hp	Output KW	0.75 kW
Frequency	60 Hz	Voltage	208-230/460 V
Current	3.95/2.10 A	Speed	1125/950 rpm
Service Factor	1	Phase	1
Duty	Continuous Air Over	Insulation Class	B
Frame	48	Enclosure	Open Air Over
Thermal Protection	Thermally Protected	Ambient Temperature	65 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Permanent Split Capacitor	Poles	6
Rotation	Counterclockwise	Mounting	Lug
Motor Orientation	Hor	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	10.46 in
Frame Length	6.07 in	Shaft Diameter	0.620 in
Shaft Extension	3.25 in	Thru-bolts Extension	N/R in
Connection Drawing	NP24X350275	Outline Drawing	5KCP39UFWD73S

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022