

PRODUCT INFORMATION PACKET

FASCO®

Model No: D335

Catalog No: D335

Fan Coil & Air Conditioner Motor, 1/20-1/30-1/40-1/60 HP, 1 Ph, 60 Hz, 115 V, 1550 RPM, 4 Speed,
4.4" Diameter, OAO



Regal and Fasco are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

| | | | |
|--------------------|---------------------|---------------------|------------------------|
| Phase | 1 | Output HP | 1/20-1/30-1/40-1/60 Hp |
| Output KW | 0.04 kW | Voltage | 115 V |
| Speed | 1550 rpm | Service Factor | 1 |
| Frame | 4.4 | Enclosure | Open Air Over |
| Thermal Protection | Thermally Protected | Ambient Temperature | 40 °C |
| Frequency | 60 Hz | Current | 2.1-1.4-1.2-1.1 A |
| Duty | Air Over | Insulation Class | A |
| UL | Recognized | CSA | Y |
| CE | N | Number of Speeds | 4 |

Technical Specifications

| | | | |
|-----------------------|----------------|--------------------|-----------------|
| Electrical Type | Shaded Pole | Starting Method | Across The Line |
| Poles | 4 | Rotation | Reversible |
| Mounting | Extended Studs | Drive End Bearing | Sleeve |
| Opp Drive End Bearing | Sleeve | Frame Material | Na |
| Shaft Type | Flat | Overall Length | 19.22 in |
| Shaft Diameter | 0.500 in | Shaft Extension | 8.00 in |
| Outline Drawing | 71085245 | Connection Drawing | SEE OUTLINE |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/25/2023