

PRODUCT INFORMATION PACKET

FASCO®

Model No: D382

Catalog No: D382

Fan Coil & Air Conditioner Motor, 1/25-1/40-1/50 HP, 1 Ph, 60 Hz, 115 V, 1550 RPM, 3 Speed,
42 Frame, OAO



Regal and FASCO are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications

| | | | |
|--------------------|------------|---------------------|-------------------|
| Phase | 1 | Output HP | 1/25-1/40-1/50 Hp |
| Output KW | 0.03 kW | Voltage | 115 V |
| Speed | 1550 rpm | Service Factor | 1 |
| Frame | 42 | Enclosure | Open Air Over |
| Thermal Protection | Automatic | Ambient Temperature | 40 °C |
| Frequency | 60 Hz | Current | 0.6/0.4/0.3 A |
| Duty | Continuous | Insulation Class | B |
| UL | Recognized | CSA | Y |
| CE | N | Number of Speeds | 3 |

Technical Specifications

| | | | |
|-----------------------|---------------------------|-------------------|--------------------|
| Electrical Type | Permanent Split Capacitor | Starting Method | Across The Line |
| Poles | 4 | Rotation | Clockwise Lead End |
| Mounting | Resilient Rings | Drive End Bearing | Sleeve |
| Opp Drive End Bearing | Sleeve | Frame Material | Na |
| Shaft Type | Flat | Overall Length | 16.77 in |
| Shaft Diameter | 0.500 in | Shaft Extension | 6.875 in |
| Connection Drawing | SEE OUTLINE | Outline Drawing | 71840016 |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:05/12/2025